

# 01

[www.goldenrules.co.kr](http://www.goldenrules.co.kr)

**Golden Rules Co.,Ltd**

Gas

**FN-Mass Flow Meter**

**KC-7730G Series**



The nation's development item, 100% domestic goods, Patent NO. 10-1606497

## APPLICATION

◆ Simply select to suit the application

Application	Type	Mass Flowmeter	
		D/P-type FN-MASS FLOWMETER	
Object of Measurement	Liquid	O	
	Gas	O	
	Vaper	O	
	steam	O	
Application	control	O	
	Monitor	O	
	Supply	O	
Operating condition	Temperature	Gas	- 40 to 100°C (Option:400°C )
		Liquid & Oil	-40 to 100°C(Option:400°C)
		Steam	-20 to 200°C(Option:400°C)
	Pressure	10 barg / 30 barg / Max 450 barg	
	Pressure loss	Negligible	
	Range ability	Large	
Installing condition	Bore	Ø10 to Ø500	
	Straight	upstream	10 ~ 7D
	Pipe length	downstream	5 ~ 2D
	Piping work		Required
	Explosion-proofing		O
Performance	Accuracy	Gas	±0.5% F.S(Option: 0.1%)
		Liquid & Oil	±0.5% F.S(Option: 0.1%)
		Steam	±0.5% F.S(Option: 0.1%)
	Velocity	Gas	0.1~100 m/s
		Liquid & Oil	0.1~100 m/s
		Steam	0.1~100 m/s

## 01 FN-MASS FLOWMETER (Gas)

### 1-2. FN-MASS KC-7730G Series



All Gas  
KC-7730G

#### Features

- Mixed gas Automatic Calculator (4~20mA input : 8-Channel)
- **5-for multi-:** Rate, integrated, volume, mass flow, temp', pressure, density
- Input Power DC 24 V, < 100mA
- Output accuracy  $\pm 0.1\%$ ,  $\pm 2.5 \mu\text{A}$  (4~20 mA, 4-Wire)
- Field validation of flowmeter calibration settings
- Smart program interface (RS-485 standard)
- Direct mass measurement of the flow function eliminates the need for additional temperature and pressure compensation
- Simple signal Processing & calibration
- Built-in flow function of compression coefficient, expansion coefficient, viscosity coefficient, direct calculation formula
- Excellent reproducibility & long-term stability
- Best price-performance ratio
- Easy adaptable for different application or into housings
- No mechanical moved components
- Greatly reduces upstream piping requirements (10-5D)
- Outstanding range ability (Turndown ratio 35:1, Option 50:1)
- 0.1-second response to changes in flow rate
- High pressure fluid can be measured (up to 400 Barg)
- High temperature fluid measurement up to 400°C
- CE, Ex(IP67)

#### Description

Golden Rules' KC-7730G Series FN-Mass flowmeter accommodates the change measurement requirements and instrument-validation demands of fluid flow monitoring installations.

It is a LOK Fitting, Flange type, and it is a microprocessor commercially capable of measuring flow rate, adjusting flow rate, and diagnosing at the same time.

Mass flow rate and totalized flow, as well as other configuration variables are displayed on the meter's optional 2X16 LCD panel. The programmable transmitter is easily configured via an RS-485 communication port and Golden Rule's KC-7730G series is a product designed based on differential pressure mass flow measurement technology.

Golden Rule's KC-7730G series is a product designed based on differential pressure mass flow measurement technology. It is a built-in flow function that takes into account the compression coefficient, expansion coefficient, and viscosity coefficient rather than the conventional temperature and pressure correction method. Enthalpy, etc. can be provided to the user.

## Performance Specifications

### ◆ Accuracy of Point Velocity

$\pm 0.5\%$  of F.S /  $\pm 1.0\%$  of R.D

(Option :  $\pm 0.1\%$  of F.S /  $\pm 0.5\%$  of R.D)

### ◆ Repeatability

$\pm 0.5\%$  of Full Scale

### ◆ Sensor Accuracy

< 0.05% of span

### ◆ Turndown Ratio

35:1 (Option 50:1)

### ◆ Pressure Loss

0.1 ~ Below 0.3 Bar

### ◆ Response Time

0.1 second

### ◆ Measuring Range

0.1 ~ 100 m/sec

### ◆ Function

**5-for multi-measurement :** rate, total, volume, mass, density, temp', pressure, energy indication

## Mass Flow Rates (Air)

Air Flow Ranges							
Pipe Size		Minimum		Maximum		Weight	
A	B	Nm <sup>3</sup> /m	Nm <sup>3</sup> /h	Nm <sup>3</sup> /m	Nm <sup>3</sup> /h	방폭	일반
15A	1/2-inch	0.13	8.0	1.33	80	5kg	3kg
20A	3/4-inch	0.27	16	2.7	160	5kg	3kg
25A	1-inch	0.4	24	120	240	6kg	4kg
40A	1 1/2-inch	0.98	59	9.8	590	7.2kg	5.2kg
50A	2-inch	1.53	92	15.3	920	8.6kg	6.6kg
80A	3-inch	3.3	200	33.3	2000	11kg	9kg
100A	4-inch	5.83	350	58.3	3500	16.2kg	14.2kg
150A	6-inch	12.7	760	127	7600		
200A	8-inch	21.7	1300	217	13.000		

Notes: Air & N<sub>2</sub> flow standard conditions :  
21°C(70°F) & 21°C(70°F) scfm:0°C Nm<sup>3</sup>/h 1Atm

## Operating Specifications

### ◆ Fluid

All Gas, Mixed Gas, Air

### ◆ Input Power

DC 24 V  $\pm 10\%$ , < 100 mA

100~240VAC  $\pm 10\%$ , < 10 Watts (Option)

### ◆ Output Signal


Linear 4 ~ 20 mA, 4Wire

RS-485

Pulse (Option)

### ◆ Pressure Drop

15.5 kpa



## Mass Flow Range 2

Air Flow Ranges							
Pipe Size		Nm3//min, SL/min		Nm3/h, kg/h		Spec'	
A	B	Min.	Max.	Min.	Max.	Fluid	Press'/Temp'
25A	1-inch	14.3 SL/min	500 SL/min				105-110KPa/ 40-60'
32A	2 ½"-inch			6.7 Nm3/h	74 Nm3/h		
40A	1 ½"-inch	142.9 SL/min	5,000 SL/min				105-110KPa/ 40-60'
50A	2-inch			14.3 Nm3/h 63 Nm3/h	500 Nm3/h 630 Nm3/h		105-110KPa/ 40-60 800 Kpa / 25°C
65A	2 ½"-inch			34.3 kg/h	1,200 kg/h		105-110KPa/ 40-60
80A	3-inch						
100A	4-inch			85.7 kg/h	3,000 kg/h		105-110KPa/ 40-60
150A	6-inch			217 kg/h	7,600 kg/h		105-110KPa/ 40-60
200A	8-inch						
250A	10-inch						
300A	12-inch	3.7 Nm3/min	135 Nm3/min	800 Nm3/h	8,000 Nm3/h		95-101 Kpa / 0.8 Bar 25°C

## N2, O2 Gas Flow Ranges

Pipe Size		Nm3//min / kg/min		Nm3/h / kg/h		Spec'	
A	B	Min.	Max.	Min.	Max.	Fluid	Press'/Temp'
25A	1-inch	1.7 8.6	60 300	145	5,100	N2 Gas O2 Gas	7-8 Bar / 20-25°C 20 Bar / 20-25°C
32A	2 ¼"-inch			10 kg/h 14.3 kg/h	100 kg/h 500 kg/h	N2 Gas O2 Gas	6.5-7 Bar / 20°C 6.5-7 Bar / 20°C
40A	1 ½"-inch			18.6 kg/h	650 kg/h	O2 Gas	7 Bar / 20°C
50A	2-inch						
65A	2 ½"-inch			2.9 kg/h 50 kg/h	100 kg/h 500 kg/h	N2 Gas O2 Gas	6.5-7 Bar / 20°C 6.5-7 Bar / 20°C
80A	3-inch			4.6 30	160 1,500	O2 Gas	10KPa / 40°C 8.8 Bar / 25°C
100A	4-inch			70	1,200	N2	7.5 Bar / 25°C

## LNG, LPG Flow Ranges

Pipe Size		Nm3//min		Nm3/h		Spec'	
A	B	Min.	Max.	Min.	Max.	Fluid	Press'/Temp'
25A	1-inch	1.7	60	3.4	120	LNG LPG	6 Bar / 20-25°C 9 Bar / 25°C
40A	1 ½"-inch						
50A	2-inch			4.3	150	LNG	5 Bar / 20°C
80A	3-inch			4.6	160	LNG	10KPa / 40°C
100A	4-inch						

**◆ Fluid & Ambient temperature**

Air : -40 ~ 100 °C (-40 ~ 212 °F) Option : 110 ~ 400°C (230 ~ 732 °F)

Pipe Temp' : Over 300 °C 이상 (572 °F)

Ambient : -4 ~ 185 °F (-20 ~ 85 °C) Option : -70 ~ 100 °C (-94 ~ 212 °F)

**◆ Pressure (limitations)**

Compression fitting : 500 psig (35 barg)

150 lb, JIS 10k RF, PN16 DIN Flange ((-40 ~ 150) °C ((-40 ~ 302) °F)) : 230 psig (15.9 barg)

150 lb, JIS 10k RF, PN16 DIN Flange (121 °C (250 °F)) : 185 psig (12.8 barg)

150 lb, JIS 10k RF, PN16 DIN Flange (400 °C (752 °F)) : 155 psig (10.7 barg)

NPT ((-40 ~ 150) °C ((-40 ~ 302) °F)) : 508 psig (35 barg)

**◆ Displays**

Display instructions: instantaneous & integration, volume, mass measurement

Alphanumeric 2 X 16 backlight LCD

Adjustable variables via remote control switch or Smart interface software

Adjustable : Full scale : (0 ~100) %

Flow: m³/h(m³), L/h(L), mL/h(mL), kg/h(kg)

Time response 0.1 sec / Correction factor setting 0.5 ~ 5 /

Zero & Span

**◆ Totalizer**

Flow rate and total oxygen point (0000. / 000.0/ 00.00 / 0.000)

Seven digits (9,999,999,99.9 Count) in engineering units Reset table by Software

**◆ Software (Option)**

Smart interface Windows® -based Software 8MB RAM of RAM, preferred 16MB of RS-485 communication

Additional features: Zero cut-off adjustment / Linearization adjustment / Save / Load configuration / For meter validation

**Physical Specification****◆ Wetted Materials**

D/P Sensor – STS316 (Option : STS316L)

Flow inline Body – STS304 (Option : STS316, STS316LS)

**◆ Enclosure**

Hazardous-Area Enclosure CASE (Ex d IIC T6 : IP67)

General-Area Enclosure CASE (IP67)

**◆ Electrical Connections**

2 X ½" PF or Exp Cable Gland(SS) 22C

**◆ Mounting (Selection)**

ANSI 150lb Flange, JIS 10k RF Flange, other

**◆ Certification**



CE (CASE)

KCS Certificate

Atex Certificate

Ex (Ex d IIC T6)

## Dimensional Spec & Chart KC-7730G



※ The shape of the sensor and housing manufacturers are subject to change

Unit : mm

Size	H	L
15A	375	300
20A	380	300
25A	390	300
32A	402	300
40A	406	300
50A	420	300
65A	442	300
80A	442	350
100A	451	400
125A	508	409
150A	540	451
200A	575	522
250A	626	602
300A	684	672


The FN-Mass flow meter realizes the following control with the current output signal.

**01** – Mass flow(kg/h) Control

**03** – Volume flow(m<sup>3</sup>/h) Control

**02** – Energy flow(MJ/h) Control

**04** – Pressure(kPa) Control



Fluid Machinery



It responds to customers' needs with a fast response speed and can realize energy savings due to ± 0.5% precision control, minimizing losses in industrial sites.

### Piping Requirement (KC-7730G FN-Mass Flow meter)

Straight Pipe Length Requirements at 1 atm			
Piping condition	KC-7730G Smart-IN™		Orifice Plate(3)
	Upstream(1)	Downstream(2)	
90° Elbow or T-Piece	10D	5D	28D
Reduction (4:1)	10D	5D	14D
Expansion (4:1)	10D	5D	30D
After Control Valve	10D	5D	32D
Two 90° Elbows (in same plane)	10D	5D	36D
Two 90° Elbows (in same plane)	10D	5D	62D

Note : (1) Number of diameters (D) of straight pipe required between upstream disturbance and the flowmeter.

(2) Number of diameters (D) of straight pipe required downstream of the flowmeter.


(3) For comparison purposes only. Table shows number of diameter(D) of upstream straight pipe length required for an ISO Standard 5167 Orifice plate with a beta ratio of 0.7

(4) Consult factory for pressure effects.


## APPLICATION

### ◆ Overview and Advantages of All-In-One FN Mass

1. Significantly reduced installation construction cost.
2. Since it is a direct type FN mass flow meter, the accuracy is much higher than the existing differential pressure type ( $\pm 0.1\%$  F.S)
3. Wide range of flow rate when measuring high temperature, high pressure and large flow rate (turndown ratio 35:1, Option 50:1)
4. Simultaneous monitoring of 5 data (flow rate, temperature, pressure, density, heat amount) by the central cancer monitoring panel with communication output
5. Easy to install as it is a temperature/pressure sensor/flow computer all-in-one mass flow meter



**Order Code KC-7730G Series (FN-MASS FLOWMETER)**



Type	Code 1
Gas	30G
Mixed gas	30MX
Blower air	30BA
<b>Hazardous-Area Location Endosure</b>	<b>FM153B</b>
Agency approved, customer specified	W

Input Power	Code 8	Calibration <sup>2</sup> (Gas)	Code 13
DC 24 V ±10 %, 60 mA	2	70 °F(21 °C) 14.7 psig (1.103 barg)	A
AC 100-240 V ±10%, 10watts(Option)	3	32 °F(0 °C) 14.7 psig (1.103 barg)	B
Agency approved, customer specified	W	Agency approved, customer specified	W

Process Connection type	Code 2
DIN Flange	D
ANSI Flange	A
JIS Flange	J
Agency approved, customer specified	W

Output Signal (Selection)	Code 9	Pressure Limit	Code 14
4-20mA, 4-Wire (Std.)	1	Low pressure	
RS-485S (Std.)	2	Below 145 psig (10 barg)	L
Agency approved, customer specified	W	Medium pressure	M
		Below 435 psig (30 barg)	(Option)
		High pressure	H
		Below 5,801 psig (400 barg)	(Option)
		Agency approved, customer specified	W

Connecion Spec <sup>1,3</sup>	Code 3,4,5		
Size	DIN	150 lb	JIS 10k
1/2" (DN15)	D2	F2	J2
3/4" (DN20)	D3	F3	J3
1" (DN25)	D4	F4	J4
1-1/4" (DN32)	D5	F5	J5
1-1/2" (DN40)	D6	F6	J6
2" (DN50)	D7	F7	J7
2-1/2" (DN65)	D8	F8	J8
3" (DN80)	D9	F9	J9
4" (DN100)	D11	F11	J11
5" (DN125)	D12	F12	J12
6" (DN150)	D13	F13	J13
8" (DN200)	D15	F15	J15
10" (DN250)	D16	F16	J16
12" (DN300)	D17	F17	J17
Agency approved, customer specified	W		

Flow Direcion	Code 11	Calibration <sup>1</sup> (Gas)	Code 12
Horizontal Left to Right or Vertical UP	1	Standard Calibration (Small Size)	A
Horizontal Right to Left or Vertical Down	2	Air, only for 1/2" and large pipe Size	
Agency approved, customer specified	W	Compressed Air, only for 2" and large pipe size	D
		Customer Calibration	B
		Agency approved, customer specified	W

Enclosure <sup>5</sup>	Code 6,7
Hazardous-Area Location Enclosure	2
IP67	N2
Agency approved, customer specified	W

## FLOW MEASUREMENT PRINCIPLE

### D/P type

FN mass flow sensor (orifice, flow nozzle, venturi nozzle, pitot)

Orifice piping pipe standard: D-0.5D / Corner / Flange

Absolute pressure and differential pressure sensor: STS316, STS316L


Temperature sensor : RTD Pt100 (3-wire)



Flow Nozzle type



Venturi Cone type



Pitot tube type

### KC-7730 Series Measurement Sensor

Golden Rule's unique FN-Mass Flow meter guarantees excellent accuracy of industrial flowmeters, and robustness and reliability in the case of high pressure and high pressure.

As a differential pressure measurement method, the sensor is a new mass flow meter that uses an orifice plate, flow nozzle, Venturi, V-Cone, Pitot tube to measure the flow rate by using a proprietary patented technology while minimizing pressure loss.

It is a new-concept mass flow transmitter that derives flow through high-level calculations under the conditions of variable physical properties of real fluids.

It is a measuring instrument that is capable of engineering in demanding conditions at industrial sites and is developed with domestic proprietary technology to minimize industrial loss and secure technological freedom, and to have excellent accuracy and stability.

In addition, it can be used in various fluids, and supplements the required intuition of the existing differential pressure flowmeter through various experimental data to maintain the desired degree in the short intuition.

By configuring the communication network (RS-485), you can monitor the progress of the mass flow meter, and install an automatic valve to control the mass flow of user settings.

The flow nozzle and orifice are manufactured according to ISO-5167 standard and ISO-9001 quality management system.

## Flow Calculator

Term	Real gas	Perfect gas
Equation of state	$pV = ZRT$	$pV = RT$
Compressibility factor	$Z$	$Z = 1$
Isothermal deviation factor	$Y = \frac{p}{V} \left( \frac{\partial V}{\partial p} \right)_T = 1 - \frac{p}{Z} \left( \frac{\partial Z}{\partial p} \right)_T$	$Y = 1$
Isobaric deviation factor	$X = \frac{T}{V} \left( \frac{\partial V}{\partial T} \right)_p = 1 - \frac{T}{Z} \left( \frac{\partial Z}{\partial T} \right)_p$	$X = 0$
Isentropic exponent ( $\kappa$ )	$\kappa = -\frac{V}{p} \left( \frac{\partial p}{\partial V} \right)_s = \frac{\gamma}{Y}$	$\kappa = \gamma = \frac{c_p}{c_v}$

## Gas expansion coefficient

$$\varepsilon = \sqrt{\left( \frac{\kappa \tau^{2/\kappa}}{\kappa - 1} \right) \left( \frac{1 - \beta^4}{1 - \beta^4 \tau^{2/\kappa}} \right) \left( \frac{1 - \tau^{(\kappa-1)/\kappa}}{1 - \tau} \right)}$$

$\kappa$  = isentropic exponent

$\tau$  = pressure ratio

$\beta$  = diameter ratio

## Flow Calculator

$$q_m = \frac{C}{\sqrt{1 - \beta^4}} \varepsilon \frac{\pi}{4} d^2 \sqrt{2 \Delta p \rho_1}$$

$$q_V = \frac{q_m}{\rho_1}$$

$q_m$  = mass flow rate [kg/s]

$q_V$  = volumetric flow rate [ $m^3/s$ ]

$\rho_1$  = upstream density [ $kg/m^3$ ]

$\Delta p$  = differential pressure [Pa]

# Delivery performance ~ 345 EA

Client	Enduser	Model
The Yoon Synergy	The Yoon Synergy	FN-MASS KC-7730A, Compressed Air
ILJIN AIR TECH	ILJIN AIR TECH	FN-MASS KC-7730A, Compressed Air
COMP KOREA	COMP KOREA	FN-MASS KC-7730A,Compressed Air ~ <b>17EA</b>
Daejeon Urban Railway Corporation	Yuseong Hot Spring Pumping Station	FN-MASS KC-7730L, Water
BELTECH CO.,LTD	BELTECH LAP	FN-MASS KC-7730L, Water
Korea Institute of Machinery and Materials	Korea Institute of Machinery and Materials	KC-7730G-FM153BEx, 25A, LPG
Sepratech Co., Ltd.	Hanwha Ulsan Plant	FN-MASS KC-7730A, Compressed Air ~ <b>4EA</b>
GTC CO., LTD.	GTC CO., LTD.	FN-MASS KC-7730A, Compressed Air ~ <b>12EA</b>
Bugang Tech	Icheon (Remnant Corpse Disposal System)	KC-7730G-FM153BEx, 25A, LPG
BELTECH CO.,LTD	Beltech test league	FN-MASS KC-7730A, Compressed Air ~ <b>4EA</b>
Sambu General Machinery	Sambu General Machinery	FN-MASS KC-7730A, Compressed Air
Gyeongsan Paper	Gyeongsan Paper	KC-7730S-FM153BEx, 250A, Steam
Act Co., Ltd.	Act Co., Ltd.	FN-MASS KC-7730A, Compressed Air ~ <b>10EA</b>
SEON BO INDUSTRY	Busan (Gupyeong 2nd Factory)	FN-MASS KC-7730A, Compressed Air
Korea Institute of Machinery and Materials	Cheonan, Chungcheongnam-do (Puritech)	KC-7730G-FM153BEx,40A,O2 Gas ~ <b>4EA</b>
Korea Institute of Machinery and Materials	Cheonan, Chungcheongnam-do (Puritech)	FN-MASS KC-7730A, Compressed Air ~ <b>4EA</b>
TURBO MAN	Iksan, Jeollabuk-do (Hite Jujeong)	KC-7730L-FM153BEx, 25A, Ethanol
Pukyong National University	YONDANG CAMPUS	FN-MASS KC-7730A, Compressed Air
DONGIL CNE	Hanwha Onsan Plant	FN-MASS KC-7730A, Compressed Air
Kunyoung Machinery	Kunyoung Machinery	FN-MASS KC-7730A, Air ~ <b>10EA</b>
SUNHWAN ENG	Kunyoung Machinery	KC-7730OP-FM153BEx, 50A, NG
SEA ANTLE	SEA ANTLE	FN-MASS KC-7730A, Compressed Air ~ <b>2EA</b>
COMP KOREA	COMPRESSED AIR	FN-MASS KC-7730A, Compressed Air ~ <b>3EA</b>
FINETECH	FINETECH	FN-MASS KC-7730A, Compressed Air ~ <b>15EA</b>
ILJIN MATERIAL	IKSAN PLANT	FN-MASS KC-7730A, Compressed Air ~ <b>2EA</b>
PURITECH	PURITECH	FN-MASS KC-7730A, Compressed Air ~ <b>4EA</b>
J KEISIS CO.,LTD.	J KEISIS CO.,LTD.	FN-MASS KC-7730A, Compressed Air ~ <b>22EA</b>
JUNG WOO FLOW	JUNG WOO FLOW	FN-MASS KC-7730A, Compressed Air ~ <b>3EA</b>
Kunyoung Machinery	Kunyoung Machinery	FN-MASS KC-7730A, Compressed Air ~ <b>10EA</b>
Wonkwang valve	STX ENGINE	KC-7730H-FM153B-G050-H2 Mixture
Kunyoung Machinery	Kunyoung Machinery	FN-MASS KC-7730GF, Compressed Air ~ <b>10EA</b>
VPE KOREA	VPE KOREA	FN-MASS KC-7730GF, Compressed Air
Kunyoung Machinery	Kunyoung Machinery	FN-MASS KC-7730GF, Compressed Air ~ <b>20EA</b>
Kunyoung Machinery	Kunyoung Machinery	FN-MASS KC-7730GF, Compressed Air ~ <b>30EA</b>
Kunyoung Machinery	Kunyoung Machinery	FN-MASS KC-7730GF, Compressed Air ~ <b>30EA</b>
BOYN E&M CO.,LTD.	Urban Railroad Corporation	FN-MASS KC-7730GF, Compressed Air
Kukdong Jeyeon	Kukdong Jeyeon	FN-MASS KC-7730WF, Water
Kukdong Jeyeon	Kukdong Jeyeon	KC-7730L-FM153B-G080-Ethylene Glycol
Korea Aerospace Research Institute	Korea Aerospace Research Institute	FN-MASS KC-7730G-FM153B, H2 Mixture ~ <b>3EA</b>
LG ELECTRONICS	Cheongju Factory	FN-MASS KC-7730S,스팀,100A,125A,200A ~ <b>3EA</b>
LG ELECTRONICS	Cheongju Factory	FN-MASS KC-7730G-FM153BEx,LNG,50A(2),65A(2),80A(1),100A,125A,150A ~ <b>8EA</b>
Kunyoung Machinery	Kunyoung Machinery	FN-MASS KC-7730GF, Compressed Air
SAMSUNG ELECTRONICS	For precise measurement of gas accumulation	KC-7730GF O2-65A, N2-32A ~ <b>2EA</b>
Korea Water Resources Corporation	Korea Water Resources Corporation	FN-MASS KC-7730SF 25A Steam, Water ~ <b>2EA</b>
Chungbuk Sewage Treatment Plant	For testing of water and wastewater facilities	KC-7730B-FM153BEx, 300A, 350A, Bio gas~ <b>2EA</b>
Innowill Co.,Ltd.	Korea Energy Research Institute	FN-MASS KC-7730GF,100A,50A,Blower Air ~ <b>2EA</b>

Client	Enduser	Model
INFORAD CO.,LTD.	Korea Energy Research Institute For vacuum pump precision flow test	FN-MASS KC-7730OP 공기 25A, 40A
Korea Energy Research Institute	Hydrogen charging station 1st and 2nd plants	KC-7730G-FM153B, H2 Mixture, 50A, 8.2barg 25.2-252 kg/h, 200'C
INNO WILL CO.,LTD.	Korea Energy Research Institute	FN-MASS KC-7730OP 50A, 65A, AIR ~ <b>2EA</b>
Toray Advanced Materials.	For precise measurement of gas accumulation	FN-MASS KC-7730OP-FM153B ~ <b>2EA</b> O2-65A, N2-32A
Energy Technology Evaluation Institute	Ammonia decomposition hydrogen production purification system	FN MASS KC-7730OP-FM153B ~ <b>2EA</b> 20A,NH3 Mix, 7.43barg, 20A-H2 Mix, 6.93barg
Korea Aerospace Industries' Sacheon site	Korean fighter KF-21 fuel system integrated rig test equipment	FN MASS KC-7730OP-FM153B ~ <b>12EA</b> JP-5,100A(2),15A(3), Liquid, 20A(6),32A(1)
Energy Technology Evaluation Institute	Alkaline water electrolysis for BOP hydrogen measurement	FN-MASS KC-7730OP-FM153B, ½", 5Nm3/h
KEPCO Electric Power Research Institute (Daejeon)	For precision measurement of hydrogen generators	FN-MASS KC-7730OP-FM153B 3/8", 200 LPM, 3-5 Barg
POSCO KWANG YANG	Nitrogen gas purification system	FN-MASS KC-7730OP, 150A, 5,000Nm3/h
POSCO Pohang Stainless Steel 3	For precise measurement of gas cutters	KC-7730OP-FM153B, 25A, LNG, O2 ~ 2EA
SK Innovation	For precise measurement of hydrogen gas	KC-7730H-FM153BEx, ½", 55-1520LPM, Nor17 Max 30Barg
Guri Sewage Treatment Plant	For precise measurement of biogas consumption	KC-7730G-FM153BEx, Bio gas, 80A ~ <b>3EA</b>
INNO WILL CO.,LTD.	Korea Energy Research Institute	FN-MASS KC-7730OP 150A, AIR
Haesung DS Co., Ltd. Changwon Headquarters	For precision measurement of semiconductor plasma process and hydrogen generator	KC-7730H-FM153BEx, 3/8", 15-150LPM, 3-5Barg
Ujin Livestock Manure Treatment Plant	For precision measurement of biogas for supply to generators	KC-7730B, Bio Gas, 50~500mmH20,,40~60'C 100A-800Nm3/h, 80A-500Nm3/h ~ <b>3EA</b>
LS Cable & System / POSCO R&D Center	For precise measurement of LNG consumption	LNG,80A,160Nm3/h,31'C,30Kpa,24V.RS-485~ <b>6EA</b>
POSCO R&D Center	For sintering steam research project	KC-7730S,Steam,250A,8-80Ton/h,193'C,8BAR
POSCO KWANG YANG	For precise steam measurement	KC-7730S,Steam,100A,7000kg/h,190'C,7Bar
Lithium Plus Geumsan Plant	Sodium hydroxide crystallization facility pjt for semiconductor fuel cell	KC-7730S,Steam,200A,150A,100A ~ <b>6EA</b> KC-7730L,Liquid,80A,40A,25A ~ <b>10EA</b>
Hyundai Motor	For precision testing of hydrogen generator	KC-7730H-FM153BEx, H2,3/8", 2-40m3/h,8.2Barg ~ <b>2EA</b>
LG Energy Solution	Daniel Gaschem Co., Ltd., for precise measurement of nitrogen gas	KC-7730G,N2 Gas,7.5Bar,70-1200Nm3/h,25'C
ECO PRO CO.,LTD.	For air precision measurement in laboratory test facilities	KC-7730G,Air,300A,130m3/min,95-101Kpa,25'C
Eumseong Livestock Manure Treatment Plant	For precision measurement of biogas for supply to generators	KC-7730B, Bio Gas, 50~300mmH20,,40~60'C 125A-125Nm3/h, 208Nm3/h ~ <b>3EA</b>
Posco Pohang	For precision measurement of air lines	KC-7730G,50A,800Kpa,25'C,63-630Nm3/h
Water Resources Corporation	Membrane filter for precise measurement of air	KC-7730G,300A,25'C,0.8Bar,800-8000Nm3/h
Daejeon Techno Park Hydrogen Electric Vehicle	For precise measurement of hydrogen gas at hydrogen charging stations	KC-7730H-FM153BEx, H2 GAS, ½", 1~10Nm3/min, 20'C, 250Bar
Ulsan Sewage Treatment Plant	For precise steam line measurement	KC-7730S-FM153BEx, Steam, 50A, 1~10Ton/h, 205'C, 17Bar
Korea Land & Housing Corporation Hwaseong Dongtan 2 Clean Energy C	For precision measurement of biogas trade	KC-7730B-FM153BEx, Bio gas, 250mmAq, 30~40'C, 50A, 20-200Nm3/h ~ <b>2EA</b> 100A, 28~280Nm3/h ~ <b>1EA</b>
Hyundai Motor	Hydrogen equipment, for precise measurement of hydrogen gas	KC-7730H-FM153BEx, 10A, H2 GAS, 5000SLPM -50~95'C, 40BAR ~ <b>3EA</b>
Posco Pohang	For precision measurement of air lines	KC-7730G,50A,800Kpa,25'C,63-630Nm3/h ~ <b>3EA</b>
Maeil Dairies Gochang Cheese Factory	For Steam EMS System Project	KC-7730S,80A,125A179'C,7.9BAR ~ <b>2EA</b>
ECO PRO CO., LTD.	For O2 Gas trading	KC-7730-FM153B, 80A, O2 Gas, 30-1,500Nm3/h 25'C, 8.8 Bar
Hyundai Rotem Tongyeong Hydrogen Refueling Station	For hydrogen gas trading	KC-7730H-FM153B,20A,2-70kg/h,40'C,200Bar ~ <b>3EA</b>
Gunpo Biomass Plant	for biogas trade	KC-7730B-FM153B,200A,120-4,200Nm3/h
Environmental Facility Management Co., Ltd.	For biogas trade	KC-7730B-FM153BEx, Bio gas, 250mmAq, 20~30'C, 100A, 10-300Nm3/h ~ <b>3EA</b>
KEPCO Research Institute	For hydrogen generator measurement	KC-7730H-FM153B,20A-20Nm3/h,100Nm3/h,40-90'C,9.7Bar, 15A-140Nm3/h, 100'C, 200Bar ~ <b>3EA</b>





**Golden Rules**

- GOLDEN RULES

[www.goldenrules.co.kr](http://www.goldenrules.co.kr)

Air & Gas & Steam & Liquid

Mass Flowmeter

Specialized manufacturer

### Distributer

Certified in accordance with

KC Q ISO 9001 : 2015

KC Q ISO 14001 : 2015

 (주)글든룰